

By submitting this order to Unitron for creation of a custom product for your client, you agree that Unitron will scan and then dispose of the ear impression, that the scan and other information generated as part of the order fulfilment process is the property of Unitron and the client has been advised that their personal information (including name, date of birth, gender, device sizing and service history) will be retained for warranty claims, product recall and statistical purposes. The information will only be released or disclosed to another person or agency when specifically requested and with your client's consent. If you would like the ear impression returned, please let us know.

OFFICE USE ONLY

Ativo RIC/BTE Order Form

Clinic	Clinic PO#			Hz	Air R L R	Bone
Hearing Care Professional				500		
Ship to Requi		Required by		1k 2k		
Client Ordered by		Ordered by		3k		
Enable War Pensions ACC Date Ordered		Date Ordered		4k 8k		
	Select a Product					
1	Ativo RIC R L		Ativo BTE	R L		
STEP 1	Ativo RIC 312		Ativo M	00		
S			Ativo SP	00		
			Ativo UP	00		
7	Select a Colour					
STEP 2	Colour Name/Number		Colour Name/Number			
<u> </u>	cotodi Name/Namber		Colour Num	c/Number		_
	Select the Coupling					
	External Receiver SDS 5.0 Receiver Length (Please select one) 0 01 02 03		Slimtube	*	Tone Hook 🔾	
			Tube Length(Pleaseselectone) 00 0 1 2 3			* not available
						with Stride UP
	Power Level Domes		Domes		Slim Tip	R L
	R L Cap Open	Small O Medium O	Cap Open O		Slimtip hard (hollow) Slimtip soft (solid)	0 0
	Moderate Vented Power Power		Vented O		,	
	Ultra Power (with cShell)	-	Powei O			
ا <mark>ه</mark> (Earmoulds Style	S R L	Material	R L
STEP	Custom Mould Are these custom products for Unitron aids purchased within the last 30 days? Yes No Wax management (cShell only)		Canal	\bigcirc	Hard Acrylic	\circ
			Canal Lock Semi-Skeleto	× ×	Silicone Soft – 70 Shore Silicone Soft – 40 Shore	
			Skeleton Half Shell Car	rved O	Silicone Soft – 25 Shore Glossy Finish	ÖÖ
	R L R L Slimtip hard (hollow) Cerustop Slimtip soft (solid) HF3 CShell CShell CShell Cocoa		Full Shell Car	ved O	Partially Satin (Hard Acrylic on Pull Cord (Hard Acrylic only)	(w) O
			Earmould colo		Tubing	R L
			only available for 5	soft moutus	Standard Wall – Dry Wall Thick Wall – Dry Wall	88
	Venting R L Intellivent (please complete the Audiogram) Note		Venting		R L	
			Intellivent (please complete the Audiogram)			
	Other to proceed as cshell O		Other			_
4	Accessories					
STEP 4	TV Connector Partner Mic Remote Control Clean n' Dry					
		ACTION COINTO	Cicuii Di	· y		